# Light Source/Laser Source FOS-120A/FLS-130A





Single- or dual-wavelength configuration 2-kHz signal generation for fiber identification Dual powering: 9 V battery and AC adapter/charger Auto-off function



电发电管

Fiber-optic T&M, monitoring, manufacturing and assembly solutions

## **Delivering Optical Source Stability**

The FOS-120A Light Source and FLS-130A Laser Source deliver excellent stability. They are compatible with the FOT-10A and FOT-20A Power Meters, which are suitable for a variety of testing applications including continuity and end-to-end testing.

#### Versatility

The FOS-120A Light Source and FLS-130A Laser Source feature single- and dual-wavelength sources from single or double ports. The units deliver continuous wave (CW) signals for power/loss measurements and 2-kHz signal generation for fiber identification. Certain FOS-120A models and all FLS-130A models are equipped with EXFO's Universal Interface.

#### **Unit Powering**

Powering options include a 9 V battery and a standard AC adapter. The battery life offers a minimum of seven hours of continuous operation. An auto-off function with a 10-minute timer is included to preserve battery life.

CW auto 2 kHz off

#### Accessories

Each unit comes complete with a rigid carrying case, a shockproof PVC holster with strap, as well as SC, ST and FC connectors.

#### **Key Features**

- Single- or dual-wavelength configuration
- 2-kHz signal generation for fiber identification
- Dual powering: 9 V battery and AC adapter/charger
- Auto-off function
- Rigid carrying case and shockproof holster with strap
- Equipped with EXFO's Universal Interface, except for certain FOS-120A models

### **Specifications**

Models	FOS-121A	F0S-122A	FOS-123A	FOS-124A	F0S-125A
Wavelength <sup>1</sup> (nm)	850 ± 30	1310 ± 40	1550 <u>+</u> 30	850 ± 30	1310 ± 30
				1310 ± 40	1550 ± 30
Spectral width <sup>2, 3</sup> (nm)	50	145	70	50/145	70/70
Launch power <sup>3</sup> (dBm)					
9/125 μm	N/A	N/A	-25	N/A	-20/-25
50/125 μm	-17	-20	-25	-17/-20	-20/-25
62.5/125 μm	-14	-16	-25	-14/-16	-20/-25
Power stability <sup>₄</sup> (dB)					
1 h	± 0.03	± 0.06	± 0.08	± 0.03/± 0.06	± 0.06/± 0.08
8 h	± 0.05	± 0.10	± 0.12	± 0.05/± 0.10	± 0.10/± 0.12
Output ports	1	1	1	2	2
output ports	I	•	•	_	L
Specifications—FLS-130A Laser Sou	· · ·	FI S-133A	FI S-135A	- FLS-136A	2
Specifications—FLS-130A Laser Sou Models	FLS-132A	FLS-133A	FLS-135A	- FLS-136A 1310 + 20	-
Specifications-FLS-130A Laser Sou	· · ·	FLS-133A 1550 ± 20	1310 ± 20	1310 ± 20	
Specifications-FLS-130A Laser Sou Models Wavelength' (nm)	FLS-132A 1310 ± 20	1550 ± 20	1310 ± 20 1550 ± 20	1310 ± 20 1550 ± 20	
Specifications-FLS-130A Laser Sou Models Wavelength <sup>1</sup> (nm) Spectral width <sup>5</sup> (nm)	FLS-132A		1310 ± 20	1310 ± 20	
Specifications-FLS-130A Laser Sou Models Wavelength' (nm)	FLS-132A 1310 ± 20	1550 ± 20	$1310 \pm 20$ $1550 \pm 20$ $\leq 5/5$	1310 ± 20 1550 ± 20 ≤ 5/5	
Specifications—FLS-130A Laser Sou Models Wavelength <sup>1</sup> (nm) Spectral width <sup>5</sup> (nm) Launch power <sup>3</sup> (dBm) 9/125 μm	FLS-132A 1310 ± 20 ≤ 5	1550 ± 20 ≤ 5	$ \begin{array}{r} 1310 \pm 20 \\ 1550 \pm 20 \\ \leq 5/5 \\ -7/-7 \end{array} $	$1310 \pm 20 \\ 1550 \pm 20 \\ \le 5/5 \\ -8/-8$	
Specifications—FLS-130A Laser Sou Models Wavelength <sup>1</sup> (nm) Spectral width <sup>5</sup> (nm) Launch power <sup>3</sup> (dBm)	FLS-132A 1310 ± 20 ≤ 5 -7	1550 ± 20 ≤ 5 -7	$1310 \pm 20$ $1550 \pm 20$ $\leq 5/5$	1310 ± 20 1550 ± 20 ≤ 5/5	
Specifications—FLS-130A Laser Sou Models Wavelength <sup>1</sup> (nm) Spectral width <sup>5</sup> (nm) Launch power <sup>3</sup> (dBm) 9/125 μm 50/125 μm 62.5/125 μm	FLS-132A 1310 ± 20 ≤ 5 -7 -7	1550 ± 20 ≤ 5 -7 -7	$1310 \pm 20 \\ 1550 \pm 20 \\ \leq 5/5 \\ -7/-7 \\ -7/-7 \\ -7/-7$	$1310 \pm 20 \\ 1550 \pm 20 \\ \le 5/5 \\ -8/-8 \\ -8/-8$	
Specifications—FLS-130A Laser Sou Models Wavelength <sup>1</sup> (nm) Spectral width <sup>5</sup> (nm) Launch power <sup>3</sup> (dBm) 9/125 μm 50/125 μm	FLS-132A 1310 ± 20 ≤ 5 -7 -7	1550 ± 20 ≤ 5 -7 -7	$1310 \pm 20 \\ 1550 \pm 20 \\ \leq 5/5 \\ -7/-7 \\ -7/-7 \\ -7/-7$	$1310 \pm 20 \\ 1550 \pm 20 \\ \le 5/5 \\ -8/-8 \\ -8/-8$	
Specifications—FLS-130A Laser Sou Models Wavelength <sup>1</sup> (nm) Spectral width <sup>5</sup> (nm) Launch power <sup>3</sup> (dBm) 9/125 μm 50/125 μm 62.5/125 μm Power stability <sup>4</sup> (dB)	FLS-132A 1310 ± 20 ≤ 5 -7 -7 -7 -7	1550 ± 20 ≤ 5 -7 -7 -7 -7	$1310 \pm 20 \\ 1550 \pm 20 \\ \leq 5/5 \\ -7/-7 \\ -7/-$	$1310 \pm 20 \\ 1550 \pm 20 \\ \le 5/5 \\ -8/-8 \\ -8/-$	

#### General Specifications-FOS-120A and FLS-130A

Size (H $\times$ W $\times$ D)	22.2 cm $ imes$ 10.3 cm $ imes$ 5.9 cm	(8 $^{3}/_{4}$ in $\times$ 4 $^{1}/_{16}$ in $\times$ 2 $^{1}/_{4}$ in)	
Weight			
unit	0.6 kg	(1.4 lb)	
shipping	1.8 kg	(4 lb)	
Temperature			
operating	-10 °C to 50 °C	(14 °F to 122 °F)	

Standard Accessories User Guide, carrying case, 9 V battery, AC adapter, protective holster, shoulder strap and Certificate of Compliance.

#### Laser Safety

21 CFR 1040.10 and IEC-60825-1

CLASS 1 LASER PRODUCT CLASS 1 LED PRODUCT

Notes


- 1. At 23 °C.
- 2. FWHM = Full width at half maximum.

3. Typical.

4. For a temperature stability of  $\pm$  1 °C.

5. rms = root mean square.

#### **Ordering Information**



Find out more about EXFO's extensive line of high-performance portable instruments by visiting our Web site at www.exfo.com							
Rugged Handheld Solutions UNIVERSAL TEST SYSTEM Optical Fiber DWDM Test Systems Protocol							
• OLTS • Power Meter • Light Source		OTDR     OLTS     ORL     ORL     Critch					
• Talk Set		Switch     Multiwavelength		5			
CORPORATE HEADQUARTERS	465 Godin Avenue	Vanier (Quebec) G1M 3G7 CANADA	Tel.: 1 418 683-0211 . Fax: 1 418 683-2170				
EXFO AMERICA	1201 Richardson Drive, Suite 260	Richardson TX 75080 USA	Tel.: 1 800 663-3936 . Fax: 1 972 907-2297				
EXFO EUROPE	Le Dynasteur, 10/12 rue Andras Beck	92366 Meudon la Forêt Cedex FRANCE	Tel.: +33.1.40.83.85.85 · Fax: +33.1.40.83.04.42				
EXFO ASIA-PACIFIC	151 Chin Swee Road, #03-29 Manhattan House	SINGAPORE 169876	Tel.: +65 6333 8241 · Fax: +65 6333 8242				
EXFO CHINA	Beijing New Century Hotel Office Tower, Room 1754-1755	Beijing 100044 P. R. China	Tel.: +86 (10) 6849 2738 · Fax: +86 (10) 6849 2662	2			
	No. 6 Southern Capital Gym Road						

EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices. **Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor.** For the most recent version of this spec sheet, please go to the EXFO website at <a href="http://www.exfo.com/support/techdocs.asp">http://www.exfo.com/support/techdocs.asp</a> In case of discrepancy, the Web version takes precedence over any printed literature.

All names, trademarks, products and services mentioned are registered or unregistered trademarks of their respective owners.

Tel.: 1 800 663-3936

TOLL-FREE (USA and Canada)

www.exfo.com • info@exfo.com

EXFÔ